


Reliance® Collection Tubs


MBRR6634E  
65.75" x 33.75" x 19.5"  
Acrylic Drop-In Tub

Soaker 115 lbs / 52 kg  
Plumbed 140 lbs / 64 kg  
Avg Fill 30 gal to above jet level  
Max Fill 80 gal to overflow

NOTE: Filling this tub to the maximum may require an above average size or dedicated water heater.



Shown with Whirlpool Package



Options Must be ordered at time of purchase

**Standard** White (no charge)  
**Color Upgrade:** Biscuit (MTISCOLOR)  
**Quick Ship / Priority** call for availability  
Soaker & Whirlpool (QSHIPMTIS)  
Airbath (QSHIPMTISA)  
**Inline Heater**  
For Whirlpool (MBHTRMTIS)  
uses existing pump  
For Soaker & Air Bath (MBHTISOAK)  
heater with recirculating pump

Accessories

**Lift and Turn Drain & Overflow**  
Chrome (MBWOC)  
White (MBWOW)  
Brushed Nickel (MBWOBN)  
**Pillows**  
Soft Pillow  
White (MBPSW) Black (MBPSB)  
Roll-Up Pillow  
Light Aqua (MBPRUC) Black (MBRUB)

Installation Aids Must be ordered at time of purchase

**Tile Flange** Factory-Installed rigid ABS  
3 sides (MBTFK3) 2 sides (MBTFK2)  
1 side (MBTFK1)  
Must specify flange location(s) on order.  
**Pre-Leveled Foam Base**  
5.5' & 6' Tubs (MBPLFOAM2)  
All airbaths include a pre-leveled foam base.

Soaker
Soaking bath - No jets. Includes textured bottom.
Part # MBSRR6634E
Air Bath
12 air jets, heated air blower, pre-leveled foam base and textured bottom. Pre-leveled foam base increases overall tub height 2"-3"
Part # MBARR6634E
Whirlpool
6 point-massage jets, 1-bhp pump and textured bottom
Part # MBWRR6634E

Hydrotherapy Package	Components Included	GFCI / 110V
Soaker with Optional Inline Heater	½-bhp pump, inline heater	1-15 amp
Whirlpool or Air Bath	1-bhp pump	1-15 amp
Whirlpool with Optional Inline Heater	1-bhp pump, inline heater	1-20 amp
Air Bath with Optional Inline Heater	heated blower, ½-bhp pump, inline heater	2-15 amp

\*CSA Certified C/US; ANSI Z124.1 and ANSI 112.19.7

Important Ordering and Installation Information

- Before ordering or installing, consider access to equipment.
- Always measure tub on-site before building tub deck.
- Use proper bedding compound to fully level and support the tub.
- Tubs equipped with an air system or factory installed pre-leveled foam base are designed to install directly onto a flat level subfloor.
- Tub height is increased up to 3" when equipped with factory-installed foam base.
- Location of all therapy components is predetermined and cannot be changed.
- Options listed cannot be combined with MTI Solutions Collection options.

• Before discarding tub crate, check for accessories that may be packaged inside.  
• All product measurements are ±1/2".  
• Specifications and configurations are subject to change without notice.  
• Measurements herein supersede all others published prior to publication revision date.

